## **DOSL** Orbital Shakers



time



175 Humboldt Street, Suite 300 Rochester, NY 14610

> Tel 800-334-7585 Fax 585-334-0241 www.dynalon.com

## **DOSL Orbital Shakers**



## **Technical Specification**

The Afon Model DOSL-2AD and DOSL-1D are shakers which provide a smooth orbital shaking action with an orbit of 16mm and speed range of 30 to 300rpm. These lab scale shakers have powerful shaking but with smooth, quite motion for long term use and can be used in environmental and CO2 incubators.

Various tray / platforms are available: The carrier type platform has four rubber cushioned horizontal securing bars with quick release handles and can be easily adjusted both vertically and horizontally to hold most sizes and types of vessel, including flasks, bottles and beakers; The flask tray can hold different sizes of the flask by changing the type of clamps.

There are two models to choose from. The digital model (1D) provides digital timer with up to 9 hours setting and speed control in 1rpm increment. The 2AD analog model provides 2-hours timers (in 10 minute integral) and 10 steps speed control at a very economical price.

Speed range (rpm) Motion Timer (min) Orbit (mm ) Maximum load (KG) Platform (mm) Dimensions, (mm, WXLXH) Operational temperature (°C ) Maximum humidity CO2 Environment Safe Net weight (KG) Power supply DOSL-2AD 10 integral selection, 30 to 300 Orbital Analog, 120 16 10 335x335 360x420x270 +4 to +40 80% yes 11 120V, 60Hz, 50W DOSL-1D Digital, 30 to 300 Orbital Digital, 540 16 10 335x335 360x420x270 +4 to +40 80% yes 11 120V, 60Hz, 50W

## **Ordering Information**

<u>Part</u>	Product Description
DOSL-01-01	LOS-2AD Orbital Shaker
DOSL-01-02	LOS-1D Orbital Shaker, Digital