## DCR Series Thermal Cycler





4104 Sylon Blvd Hainesport, NJ 08036

Tel 609-326-3190 www.accuthermal.com

# DCR Series



## DyNAcycler DCR

- · Full sized workhorse
- Easy programming
- Wide Temperature Range



#### **Technical Specification**

**Temperature** Temperature range 4°C to 99°C ± 0.5°C Block uniformity Temperature accuracy ± 0.5°C End of program cooling below ambient YES

Maximum ramp rate 2.3°C/second

**Heated Lid** 

100°C to 115°C Heated lid temperature

Heated lid enable/disable YES

**Programming** 

YES Program naming using alpha keys Program password protection YES Number of programs (3 step) 37

**Dimensions** 

Height 260 mm Width 220 mm Length 420 mm Weight 12.0 Kg

Power

**AC INPUT** 120V or 230V with switch



### **Ordering Information**

Part **Product Description** DCR60 DCR NON Gradient Thermal Cycler for 60 x 0.5ml microtubes, 120V/230V DCR96 DCR NON Gradient Thermal Cycler for 96 x 0.2ml microtubes, 120V/230V

Tel 609-326-3190